

NEBO  
MYCRO<sup>®</sup> 250  
HEADLAMP & CAP LIGHT

- LIGHT MODES**
- High (250 lumens) - 1 hour / 65 meters
  - Medium (50 lumens) - 2 hours / 28 meters
  - Low (15 lumens) - 5 hours / 15 meters

- DESIGN**
- USB-C rechargeable
  - Detachable cap light clip with adjustable tilt
  - Battery charging indicator
  - Water and dust-resistant (IP44)

- OPERATION**
- Side-positioned button controls power and mode selection

- ACCESSORIES**
- 2 adjustable head straps; one size fits all
  - 1 USB-A to USB-C charging cable

- BATTERIES**
- Powered by internal rechargeable battery (Recharge time: 1.5 - 2 hours)

- SPECS**
- 0.3 lbs.
  - (H) 1.75" x (W) 2.75" x (D) 0.6"



2-PACK  
HEADLAMP & CAP-LIGHT

The MYCRO 250 is a **rechargeable headlamp and cap-light** that includes an adjustable head strap. Small enough to fit in the palm of your hand, the **integrated tilt feature** allows you to position the beam exactly where you want it.

UPC CODE	ITEM	CASE
645397941064	NEB-HLP-1010	12



CALIFORNIA REQUIRED ⚠️ WARNING | Cancer and Reproductive Harm | [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)



**PDQ Dimensions**  
(H) 1.92" x (W) 6.3" x (D) 9.4"  
**Natralock Dimensions**  
(H) 8.65" x (W) 4.88" x (D) 1.5"

