

NEBO

BLACKOUT BACKUP™ EMERGENCY LED BULB

LIGHT MODES

- Fixture (850 lumens): 24 meters
- Backup High (500 lumens): 2 hours / 18 meters
- Backup Medium (185 lumens): 6 hours / 9 meters
- Backup Low (80 lumens): 12 hours / 6 meters

DESIGN

- Remains on without power
- Replaces standard (A70/A21) bulbs with E26 base
- Soft, white light (3,000K)
- 60W equivalent

OPERATION

- Standard screw base - turn ON fixture to activate
- Power cap with button - press to activate

ACCESSORIES

- Power cap for handheld use

SPECS

- 0.3 lb.
- (H) 5.12" x (W) 2.56" x (D) 2.56"



CALIFORNIA REQUIRED ⚠️ WARNING | Cancer and Reproductive Harm | www.P65Warnings.ca.gov



Actual Size



REMAINS ON EVEN WITHOUT POWER

The Blackout Backup™ Emergency LED Bulb functions just like a standard bulb, using a wall or lighting fixture, but its **rechargeable internal battery** stays charged and ready to provide your home with up to **12 hours of emergency lighting** during power outages.

UPC CODE	ITEM	CASE
645397940586	NEB-ARE-0003	12
645397941866	NEB-DSP-0036	1

FREE WITH 48 PIECE ORDER

Floor Display Dimensions
(H) 51.5" x (W) 13.87" x (D) 12.4"

Box Dimensions
(H) 5.51" x (W) 2.84" x (D) 2.84"
PDQ Dimensions
(H) 9" x (W) 7" x (D) 11.78"

