


RPVM 19" Mesh Vented Rack Panel's


The RPVM from Pulse is a range of 19" mesh vented rack panels allowing air ventillation and heat dissipation for rack equiment mounted in 19" rack cabiniets, enclosures and flight cases.

- 19" Rack mount panels
- · Steel plate with a black powder coating
- Punched vent holes (mesh style) allows greater air flow over slotted vents
- · Pressed angled edging for added strength
- Available in 1U, 2U, 3U 4U & 6U rack heights

Model	U-Height	Н*	W*	D*
RPVM1	10	44.5	482.5	11
RPVM2	2U	89	482.5	11
RPVM3	3U	133.5	482.5	11
RPVM4	4U	178	482.5	11
RPVM6	6U	267	482.5	11

^{*} Dimensions in mm, ±0.25mm





The specifications above are correct at the time of printing this data sheet. For improvement purposes, all specifications for these units, including design and appearance, are subject to change without prior notice.

