

Product information

12 72 190

KNIPEX NexStrip

Multi-Tool for Electricians



- Perfect crimping: fast and even square crimping for individual wire ferrules, the ratchet crimping mechanism guarantees the required crimping pressure
- Precise stripping: automatically adapts to the respective cable diameter and ensures consistent stripping lengths with the adjustable length stop especially with repetitive work
- Multi-component grips ensure non-slip, comfortable handling
- Quick, precise square crimp of single wire ferrules according to DIN 46228 parts 1+4, self-adjusts for sizes 0.25 – 4 mm² / 2 x 2.5 mm² – allows for quick crimping between different sizes
- Repetitive, high crimping quality due to ratcheting mechanism with a complete crimping cycle
- Stripping with fine adjustment for optimal adjustment to special materials or temperature conditions for flexible and solid conductors between 0.03 and 10 mm² (AWG 32-8)
- Cleanly cuts conductors up to 10 mm² (AWG 8)
- High-quality housing made of glass fibre reinforced plastic
 For the electrical trade: for domestic installations and wiring
- For the electrical trade: for domestic installations and wiring of electronical devices, such as PLC (programmable logic controller)
 Wire stripper with three functions: stripping wire up to 10 mm²,
- Whe supper with three functions: supping wire up to 10 mm², crimping capacity of 4 mm² or 2 x 2.5 mm² and cutting capacity of 10 mm²

General

Article No.	12 72 190
EAN	4003773088165
Weight	170 g
Dimensions	190 x 17 x 110 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

technical change and errors excepted





KNIPEX Quality – Made in Germany
















KNIPEX Quality – Made in Germany















KNIPEX Quality – Made in Germany













