



RC007B REMOTE ELB3 KIT

Remote 3 Hour Emergency Kit suitable for RC007B Panels

Product data

General Information

Lamp family code	
Light source color	NA
Light source replaceable	No
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Luminaire light beam spread	-
Emergency lighting	Basic (3h)
Ingress protection rating	IP20
Dimmable	No
Installation Method	Remote Kit
Manufactured to Standards	EN60598-1 & EN60598-2-22
Weight	0.3kg

Operating and Electrical

Input Voltage	230-240V AC
Input Frequency	50 to 60 Hz
Class / IP / IK	Class II / IP20 / IK03
Battery type	LiFePO4 6.4V 1.6Ah
Emergency Power	2W
LED Voltage range	10-80V DC
Temperature	5°C~35°C
Warranty	5 Years (2 year battery)

Mechanical and Housing

Luminaire Dimensions	245mm x 67mm x 32mm
Housing Construction	Polycarbonate housing
Body colour	Black
Minimum Ceiling Cut-out Size	75mm Diameter

Product Data

Full product code	919013004905 RC007B REMOTE ELB3 KIT
-------------------	-------------------------------------

Wiring Instructions & Dimensions

