

PC B 65 G

FIBOX
Enclosing innovations



Sample image

Order symbol : PC B 65 G

Product nr : 8724303

UL Name : UL PC B 65 G

Description : Enclosure, PC




Remarks : Grey cover

EAN : 6418074001955

El. number :

- Finland : 3423401
- Denmark : 8212001475
- Sweden : 2536801

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and polyamide cover screws.



Dimensions :

	Height	Width	Depth
mm :	110	80	65
inch :	4.33	3.15	2.56

Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Accessories :

B-MP	Mounting plate, for enclosures: (80 x 54 x 1)
FP 22040	Wall fastening lug (2 pcs), for enclosures:
B-3	DIN-35 Mounting rail, for enclosures: (80 x 35 x 1)

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960C

Certificates :

SGSFIMKO_PICC_pc