

## Coaxial PCB Connector 96\_MMPX-50-0-3/111\_N

### Description

Straight PCB jack

Interface Standards

HUBER+SUHNER MMPX STD (Patent US 7.294.023)



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$		
Interface frequency max.	67 GHz		
Frequency range	DC to 26.5 GHz	26.5 to 50 GHz	50 to 67 GHz
Return loss	$\geq 25$ dB	$\geq 15$ dB	$\geq 10$ dB

#### Mechanical Data

Board mounting type	pin-in-hole / SMT
Weight	0.0004 kg

#### Environmental Data

Operating temperature	-65 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

### Related Documents

Outline drawing	DOU-00157033
-----------------	--------------

### Ordering Information

Bulk 10 pcs package	96_MMPX-50-0-3/111_NM-1
Tape and Reel package	96_MMPX-50-0-3/111_NM

### Remarks

Decoupling tool MMPX shall be used (74\_Z-0-0-491/74\_Z-0-0-555)!