

Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna



## LCMARRM02

### Features

- Stainless steel marine grade mount
- Dual swivel ratchet style
- 1"-14 male threaded
- Heavy duty
- Mirror polish
- Anti corrosion material
- Flat base fixture

### Applications

- Marine antenna mounts
- Marine communication: VHF, GPS, satellite phones
- Navigation: Radar, sonar, depth finders
- Fishing: Fish finders, sonar-based equipment
- Entertainment: Satellite TV, radio systems
- Emergency services: Search and rescue operations

### Description

The L-com LCMARRM02 dual swivel ratchet style antenna mount is offered for marine and omnidirectional antennas. This marine antenna mount is constructed of anti-corrosion stainless steel with a mirror polish. Our heavy-duty mount is ideal for marine communication, fishing, navigation, entertainment, and emergency services.

The working temperature range for our dual swivel ratchet-style installation is -40 to 80 degrees Celsius. The LCMARRM02 marine antenna mount from L-com is available in 8-inch length, 2.52-inch width, and 5.5-inch height. This antenna mount has a flat base fixture and 1"-14 male threads, making it suited for use with search and rescue equipment, satellite TV, radio systems, radar, sonar, depth finders, VHF, GPS, satellite phones, fish finders, and sonar-based equipment applications.

L-com has one of the largest in-stock selections of marine grade dual swivel ratchet style antenna mounts for international and domestic orders. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect stainless steel marine antenna mount for your requirements.

### Mechanical Specifications

#### Size

Length	8 in [203.2 mm]
Width	2.52 in [64.01 mm]
Height	5.5 in [139.7 mm]
Weight	1.32 lbs [598.74 g]

### Environmental Specifications

Operating Temperature, Min	-40 deg C
Operating Temperature, Max	80 deg C
Material	Stainless Steel

Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers,

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna](#)

Casting Heavy Duty 4-way Ratchet Marine mount with  
Standard 1"-14 male threads for marine antenna

## LCMARRM02



passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Casting Heavy Duty 4-way Ratchet Marine mount with Standard 1"-14 male threads for marine antenna

L-com CAD Drawing

