

WI-M-8-XX-@

(Extra Heavy-Duty 8 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



• Mueller's WI-M-8-@ is 8 AWG, 1650/0.08 stranded, tinned copper wire with highly flexible 0.256" (6.5mm) diameter silicone jacket.

• Ratings: Voltage 1100V

Current 90A @ 75°C

120A @ 104°C

180A @ 150°C

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

Dielectric Strength 3.2 KV/Min

Spark Test 10 KV

Rated Temperature -40°C to 200°C

Flammability Rating FT2 UL Recognition 3640

- Length: The "XX" in the model number indicated length in feet. Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.

Available colors: -0 Black, -2 Red