

## WI-M-14-XX-@

(Extra Heavy-Duty 14 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-14-@ is 14 AWG, 420/0.08 stranded, tinned copper wire with highly flexible 4.7mm diameter silicone jacket.
  - Ratings:

Voltage 1100V

Dielectric Strength 3.2 KV/Min

Spark Test 10 KV

Rated Temperature -40°C to 180°C

Temperature Rating FT2 UL Recognition 3640

- Length: The "XX" in the model number indicated length in feet. Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.

Available colors: -0 Black, -2 Red

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524