

Product Datasheet

252.SA.1 Product code:

Product type: Plastic Tip Tweezers

Made in: Switzerland

Description: Type 252CF soft tip tweezers are suitable to applications which require holding a flat, soft

component firmly. The Carbon Fiber reinforced ESD Plastic provides the tweezers with ESD

and non-scratching properties.

Tip description: straight, wide, short

Plastic reinforced with Carbon Fiber (CF) Tip material:

Coating/finishing: Sandblasted

Body material: Anti-Magnetic Anti-Acid Stainless Steel (SA)

Picture:






Tweezer dimensions: OAL 116.0 mm - 4.567 inch

> Width 10.5 mm - 0.413 inchHeight 15.0 mm - 0.591 inch

Tip details:



Dimensions mm



Dimensions inch

Tip dimensions: Tip width 8.20 mm - 0.323 inch

Tip thickness 0.50 mm - 0.020 inch

ideal-tek.com_ REV.00 - 22.11.2022