()ideal-tek

Product Datasheet

Product code:	361	
Product type: Made in:	High Precision Scissors	
Description:	The 361 are high precisi access small areas, idea stuck in the material. The 55HRC hardness.	
Tip description:	curved, extra fine	

h precision scissors with extra fine blades and a spear shape which allows to eas, ideal for miniature work. The curved blades prevent the tips from getting erial. The Inox material is suitable for cleaning. The blades are hardened to S.

Coating/finishing: Sandblasted

Stainless Steel (S) **Body material:**

Picture:



Product dimensions:	OAL	90.0 mm – 3.543 inch
	Width	45.0 mm – 1.772 inch
	Height	5.0 mm – 0.197 inch
Tip dimensions:	Tip width	0.40 mm – 0.016 inch
		s 0.30 mm – 0.012 inch

