

Product Datasheet

Product code: ES6023B.CR.BG

Product type: High Precision Pliers

Made in: Switzerland

Description: The 6023B is a high precision plier belonging to the long snipe nose plier family. The long

bent jaw length improves the ease of the hold. The curved geometry provides maximum visibility. The smooth surface on the jaw prevents scratches while holding. The 6023B is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The jaw are

hardened to 45HRC hardness.

Head description: Bent, Bent Nose

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:





Dimensions: OAL (A) 141.0 mm – 5.551 inch

Width 60.0 mm - 2.362 inch

Height 18.0 mm - 0.709 inch


Head

dimensions: Width (C) 10.0 mm - 0.394 inch

Thickness (D) 6.4 mm - 0.252 inch B 30.0 mm - 1.181 inch E 1.0 mm - 0.039 inch

F 0.5 mm – 0.020 inch

10.0 56.4 1.0 60° 0.5



ideal-tek.com_____