## ()ideal-tek

## **Product Datasheet**

Product code:	2WFG.SA.1
Product type:	Wafer Tweezers
Made in:	Switzerland
Description:	Type 2WFG wafer tweezers are suitable to delicate applications which require holding a 2- inch flat component firmly. The line serration provides the handles with extra grip. The bent paddle helps to hold the component still during positioning while the grid helps to remove excess liquid.
Tip description:	straight, wafer
Coating/finishing:	Sandblasted
Body material:	Anti-Magnetic Anti-Acid Stainless Steel (SA)
Picture:	
Tweezer dimensions	CAL = 120.0  mm - 4.724  inch Width = 10.0 mm - 0.394 inch Height = 11.5 mm - 0.453 inch
Tip details:	0.150 0.118 0.256 0.256 0.256 0.256 0.354 Dimensions inch 0.150 0.256 0.354 Dimensions inch 0.150 0.16 0.17 0.1
Tip dimensions:	Tip width $6.50 \text{ mm} - 0.256 \text{ inch}$ B $9.00 \text{ mm} - 0.354 \text{ inch}$ C $3.00 \text{ mm} - 0.118 \text{ inch}$ D $3.80 \text{ mm} - 0.150 \text{ inch}$

E 3.00 mm – 0.118 inch