

## **Product Datasheet**

Product code: 65A.SA.0

**Product type:** High precision tweezers

Made in: Switzerland

**Description:** Type 65A high precision tweezers are suitable to delicate applications which require holding a

small component firmly while granting maximum visibility. The bent geometry provides

maximum visibility and increased ergonomics.

**Tip description:** bent, very fine, very sharp, superior finish

Coating/finishing: Sandblasted

Body material: Anti-Magnetic Anti-Acid Stainless Steel (SA)

Picture:






Tweezer dimensions: OAL 140.0 mm - 5.512 inch

Width 9.0 mm – 0.354 inch Height 11.0 mm – 0.433 inch

Tip details:



0.006 30° 0.004

Dimensions inch

**Tip dimensions:** Tip width 0.15 mm - 0.006 inch

Tip thickness 0.09 mm - 0.004 inch