

Product Datasheet

Product code: E5352.CR.BG

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5352 is a high precision cutter belonging to the large tapered cutter family. This type of

geometry and head dimensions offer an advantage to support the cut. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5352 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC

hardness.

Head description: Large Tapered

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.20-1.20 mm (32-17 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek - Thermoplastic Elastomer + PP compound

Picture:





Dimensions: OAL (A) 125.0 mm – 4.921 inch

Width 60.0 mm – 2.362 inch

Height 21.0 mm - 0.827 inch

Head

dimensions: Width (C) 12.0 mm - 0.472 inch

Thickness (D) 6.4 mm - 0.252 inchB 12.0 mm - 0.472 inchF 0.2 mm - 0.008 inch



