

D-XTV 10 - End cover

1329608

<https://www.phoenixcontact.com/in/products/1329608>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

End cover, length: 72 mm, width: 2.2 mm, height: 42.6 mm, color: gray



Commercial Data

Item number	1329608
Packing unit	50 pc
Minimum order quantity	50 pc
Sales Key	BE2
Product Key	BE2Z1X
GTIN	4063151624378
Weight per Piece (including packing)	5.23 g
Weight per Piece (excluding packing)	5.23 g
Customs tariff number	85389099
Country of origin	CN

D-XTV 10 - End cover



1329608

<https://www.phoenixcontact.com/in/products/1329608>

Technical Data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	2.2 mm
Height	42.6 mm
Height NS 35/15	57.6 mm
Height NS 35/7,5	50.1 mm
Length	72 mm

D-XTV 10 - End cover



1329608

<https://www.phoenixcontact.com/in/products/1329608>

Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 8.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in