



## TM2S8-C Cable Tie Mount, Natural, PA 6.6, 0.63x0.43", #8 Screw, PK100

TM2S8-C

Panduit TM2S8-C screw applied cable tie mounts offer a through hole in the mount in which a screw or rivet can be secured, this offers maximum stability for cable bundles. Install with a #8 (M4) screw. Suitable for miniature, intermediate and standard cross-section cable ties. Made of Nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. They are 0.43" (10.9 mm) wide, are natural in color and come in packages of 100.

## **Specifications**

Application	Unique Cradle Design Provides Maximum Stability for the Cable Bundle and Low Profile Design Keeps Bundle Close to Mounting Surface
Product Type	Cable Tie Mount
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Screw
Mounting Hole Thread Size	#8
Overall Height (In.)	0.275
Overall Height (mm)	7
Overall Length (In.)	0.63
Overall Length (mm)	16
Overall Width (In.)	0.43
Overall Width (mm)	10.8
Standards Met	CE Compliant, UL Recognized:E136577, RoHS Compliant
For Use With	Miniature, Intermediate, Standard Cross-Section Ties



## **Packaging Detail**

UPC	07498358220
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0266
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.1329