

PRODUCT-DETAILS

10RC-14

INS VINYL RING TERM 12-10 1/4IN YEL



General Information

Extended Product Type	10RC-14
Product ID	7TAI029450R0003
EAN	5414363136224
Catalog Description	INS VINYL RING TERM 12-10 1/4IN YEL
Long Description	Vinyl-Insulated Ring Terminal, Length 1.16 Inches, Width .50 Inches, Maximum Insulation .210, Bolt Hole 1/4 Inch, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

Ordering

EAN	5414363136224
UPC	786210800462
Country of Origin	United States (US)
Selling Unit of Measure	each

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	250 piece
Package Level 2 Width	10.3 in 262 mm
Package Level 2 Height	8.1 in 206 mm

Package Level 2 Depth / Length	12.1 in 307 mm
Package Level 3 Units	2500 piece
Package Level 3 Width	8 in 203 mm
Package Level 3 Height	10 in 254 mm
Package Level 3 Depth / Length	11.8 in 300 mm

Additional Information

Brand / Label	Sta-Kon
Color	Yellow
Effective Date	19750812
Material	Copper
Product Name	Electrical terminal<1000v
Product Type	Vinyl Insulated Ring Terminal
RoHS Date	9AKK107992A8991
Special Functions	These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wires flex point. Braze seam barrel is serrated to obtain high pull-out value.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	12-10 AWG

Certificates and Declarations

Data Sheet, Technical Information	10RC-14
-----------------------------------	---------

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
ETIM 8	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

