

# Part Number: P-XX-K2RF0-F2

Panel Interface Connector with Panel Mount Housing; UL Type 4X; Standard GFCI Duplex Outlet; No Circuit Breaker

<https://shop.graceport.com/products/p-xx-k2rf0-f2>



## Product Specifications

### Description Detail

Panel Interface Connector that typically mounts to the outside of a control panel housing. These programming ports eliminate the need to open the panel door and improve safety and compliance to NFPA 70e. We offer 15,000+ combinations of components and outlets.

### Electrical Specifications

Power Type	Domestic GFCI Inside-Outside Rear Outlet
Power VAC	125
Power AMPs	20
SCCR Rating	2kA


### Geometric Data

Width	5.08 in
Height	3.54 in
Depth	1.60 in





### Commercial Data

Country of Origin	US
Schedule B Code	8537.10.9090

### CAD Files

File Format	
2D PDF File	

### Datasheets

Name	
GracePort Datasheet	
GracePort Datasheet Spanish	
Inside-Outlet Installation Guide	
Panel Mount Housing Installation Guide	

### Don't see what you're looking for?

Contact us at [sales@gracetechnologies.com](mailto:sales@gracetechnologies.com), call 1-800-280-9517 or visit [www.graceport.com](http://www.graceport.com) to chat with our customer service.