



8755 W. Higgins Road
Suite 500
Chicago, Illinois USA 60631

Jul 11th, 2023

Notification of IXYS Brand Schottky Diode Discrete MOQ Change _Phase 2

To whom it may concern,

This is a declaration letter associated to

[Phase 2] ESW490-42 – IXYS Brand Schottky Diode Discrete Alternative Qual Status, Littelfuse will change the MOQ for IXYS Brand Schottky Diode Discrete products aligning to manufacture requirement. Detail affected part number list refer to Appendix.

There will be no change on product fit, form, function.

We value your business and look forward to assisting you whenever possible. Thank you!

Sincerely and Best Regards,

Sophia Lv
Global Product Manager
Thyristor and Rectifier Diode
Semiconductor Business Unit, Wuxi, China
+86 510 85277701 - 7967
slv@littelfuse.com

Appendix --- MOQ change table for Affected Products

Material	OLD MOQ	OLD MPQ	NEW MOQ	NEW MPQ
DSA10C150PB	50	50/TUBE	32,000	50/TUBE
DSA10C150UC-TRL	2,500	2500/TR	32,000	2,500/TR
DSA10C150UC-TUB	50	50/TUBE	32,000	2,500/TR
DSA10I100PM	50	50/TUBE	32,000	50/TUBE
DSA10IM100UC-TRL	2,500	2500/TR	32,000	2,500/TR
DSA10IM100UC-TUB	50	50/TUBE	32,000	2,500/TR
DSA15I45PA	50	50/TUBE	32,000	50/TUBE
DSA15IM150UC-TRL	2,500	2500/TR	25,000	2,500/TR
DSA15IM150UC-TUB	50	50/TUBE	25,000	2,500/TR
DSA15IM200UC-TUB	70	70/TUBE	25,000	2,500/TR
DSA15IM45IB	50	50/TUBE	32,000	50/TUBE
DSA15IM45UC-TRL	2,500	2500/TR	32,000	2,500/TR
DSA15IM45UC-TUB	50	50/TUBE	32,000	2,500/TR
DSA20C100PB	50	50/TUBE	32,000	50/TUBE
DSA20C100PN	50	50/TUBE	32,000	50/TUBE
DSA20C200PB	50	50/TUBE	32,000	50/TUBE
DSA20C45PB	50	50/TUBE	32,000	50/TUBE
DSA20C60PB	50	50/TUBE	32,000	50/TUBE
DSA30C100PB	50	50/TUBE	24,000	50/TUBE
DSA30C100PN	50	50/TUBE	24,000	50/TUBE
DSA30C100QB	30	30/TUBE	27,000	30/TUBE
DSA30C150PC-TRL	800	800/TR	16,000	800/TR
DSA30C150PC-TUB	50	50/TUBE	16,000	800/TR
DSA30C200IB	50	50/TUBE	16,000	50/TUBE
DSA30C200PC-TRL	800	800/TR	16,000	800/TR
DSA30C200PC-TUB	50	50/TUBE	16,000	800/TR
DSA30C45PB	50	50/TUBE	24,000	50/TUBE
DSA30C45PC-TRL	800	800/TR	24,000	800/TR
DSA30C45PC-TUB	50	50/TUBE	24,000	800/TR
DSA30C60PB	50	50/TUBE	24,000	50/TUBE
DSA60C100PB	50	50/TUBE	16,000	50/TUBE
DSA60C45PB	50	50/TUBE	16,000	50/TUBE
DSA60C60PB	50	50/TUBE	16,000	50/TUBE
DSB10I45PM	50	50/TUBE	32,000	50/TUBE
DSB15IM30UC-TRL	2,500	2500/TR	32,000	2,500/TR
DSB15IM30UC-TUB	50	50/TUBE	32,000	2,500/TR
DSB15IM45IB	50	50/TUBE	32,000	50/TUBE
DSB20C60PN	50	50/TUBE	32,000	50/TUBE
DSB20I15PA	50	50/TUBE	32,000	50/TUBE
DSB30C30PB	50	50/TUBE	24,000	50/TUBE
DSB30C45PB	50	50/TUBE	24,000	50/TUBE
DSB30C60PB	50	50/TUBE	24,000	50/TUBE
DSB60C30PB	50	50/TUBE	8,000	50/TUBE
DSB60C45PB	50	50/TUBE	8,000	50/TUBE
DSB60C60PB	50	50/TUBE	8,000	50/TUBE

DSS10-006A	50	50/TUBE	32,000	50/TUBE
DSS10-01AS-TRL	800	800/TR	32,000	800/TR
DSS10-01AS-TUB	50	50/TUBE	32,000	800/TR
DSS16-0045A	50	50/TUBE	32,000	50/TUBE
DSS16-0045AS-TRL	800	800/TR	32,000	800/TR
DSS16-0045AS-TUB	50	50/TUBE	32,000	800/TR
DSS16-01AS-TRL	800	800/TR	32,000	800/TR
DSS16-01AS-TUB	50	50/TUBE	32,000	800/TR
DSS25-0025B	50	50/TUBE	24,000	50/TUBE
DSS25-0045A	50	50/TUBE	16,000	50/TUBE
DSS6-0025BS-TRL	2,500	2500/TR	32,000	2,500/TR
DSS6-0025BS-TUB	70	70/TUBE	32,000	2,500/TR
DSS6-0045AS-TUB	70	70/TUBE	32,000	2,500/TR
DSS6-015AS-TUB	70	70/TUBE	32,000	2,500/TR
DSSK10-018A	50	50/TUBE	16,000	50/TUBE
DSSK16-01A	50	50/TUBE	24,000	50/TUBE
DSSK16-01AS-TRL	800	800/TR	24,000	800/TR
DSSK16-01AS-TUB	50	50/TUBE	24,000	800/TR
DSSK18-0025BS-TRL	800	800/TR	24,000	800/TR
DSSK18-0025BS-TUB	50	50/TUBE	24,000	800/TR
DSSK20-0045B	50	50/TUBE	24,000	50/TUBE
DSSK28-0045BS-TRL	800	800/TR	8,000	800/TR
DSSK28-0045BS-TUB	50	50/TUBE	8,000	800/TR
DSSK28-006BS-TRL	800	800/TR	8,000	800/TR
DSSK28-006BS-TUB	50	50/TUBE	8,000	800/TR
DSSK28-01AS-TUB	50	50/TUBE	16,000	800/TR
DSSK38-0025B	50	50/TUBE	8,000	50/TUBE
DSSK38-0025BS-TRL	800	800/TR	8,000	800/TR
DSSK38-0025BS-TUB	50	50/TUBE	8,000	800/TR
DSSK48-003BS-TUB	50	50/TUBE	8,000	800/TR
DSSK48-003BS-TRL	800	800/TR	8,000	800/TR