



## Cat 6 Angled Punchdown Patch Panel, 24 Port, 1 RU

DPA24688TGY

Punchdown patch panel, 24-port, angled, black

### Specifications

Note	DPA24688TGY replaces DPA24688TG
Product Type	Patch Panel Kit
Termination Style	Punchdown
Patch Panel Style	Angled
Performance Level	Category 6
Material	CRS
Wiring Scheme	T568A/T568B
Number of Ports	24
Number of Rack Units	1
Overall Width (In.)	19
Overall Width (mm)	482.6
Sub Brand	Pan-Net®
Overall Depth (In.)	4.75
Overall Depth (mm)	120.6
Overall Height (In.)	1.25
Overall Height (mm)	31.8
Identification Type	Adhesive Label
Color	Black
Standards Met	Exceeds channel and component requirements of ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards at swept frequencies 1 to 250 MHz. Meets all applicable ANSI/TIA-968-A requirements; Meets IEC 60603-7, Supports IEEE 802.3af, 802.3at, and IEEE 802.3bt type 3 and 4 for PoE applications up to 100 W, UL 1863 approved, RoHS Compliant
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Overall Length (In.)	4.75
Overall Length (mm)	120.6

**Packaging Detail**

UPC	07498303715
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.2735
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	2.7352