



CRI-3350 | HIGH CRI WORK LIGHT

- 3350 lumen 30W high CRI 96+ COB LED
- 5 Colour Temperatures - CCT range: 2700K / 3500K / 4500K / 5500K / 6500K
- Dual power - rechargeable & mains
- Memory switch - remembers last mode used
- Super tough aluminium, nylon & TPR structure
- Built in aluminium heat sink
- 180° adjustable stand/handle with hole for attaching to tripod/magnet
- IP65 dust & water resistance
- IK07 shock resistance
- Battery level & charging indicators
- Mains 5M multi-country charger/power lead included
- Fast 3.5 hours charge time

BATTERY 11.1v 5200mAh Li-ion
WEIGHT 1150g
DIMENSIONS 224 x 199 x 74mm



LUMEN 3350LM | RUNTIME 2.5-9H | BEAM 62M | IP RATING IP65/IK07