









MTB-5300 | MULTI BATTERY HYBRID WORK LIGHT

- Ultra bright 5300 lumen 50W 6500K COB LED
- Hybrid rechargeable and mains powered
- Takes up to 20V 6.0A batteries from Milwaukee, De Walt, Makita & Metabo - 4 adaptors included
- Super tough heavy duty nylon construction
- Easy carry rubber grip handle
- Rotating stand/base with holes for tripod/magnet
- 4 x dim settings: 650 / 1350 / 2700 / 5300 lumen
- Secure battery compartment cover (note: larger 6ah batteries may need to be used without cover)

BATTERY Not included, bare tool

WEIGHT 1250g

DIMENSIONS W 238 x H 257 x D 181mm

- Safety automatic switch-over from mains to battery in the event of power failure
- 2A USB PowerBank works with any battery installed
- 4 x Battery level and charging indicators
- Comes with 5 metre heavy duty 24V-2.7A H05RN-F charger/power lead (includes UK, EU, US & AU adaptors)
- Unilite 14.8V 5.2Ah battery available to purchase separately (NOTE: Only the Unilite battery can be charged via the lamp)

NOTE: runtimes based on Unilite 5.2Ah battery

LUMEN 5300LM | RUNTIME approx 2.5-16H | BEAM 95M | IP RATING IP65/IK07

WWW.UNILITE.CO.UK #BUILT TOUGH