



MASTER GLASS LED candles and lustres



MAS LEDCandleDT3.4-40WE14 927B35CLGUK

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lustres with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cosy atmosphere. The MASTER LED candles and lustres can be dimmed for different lumen level and also for the different colour temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED. They provide excellent quality of light. By offering a lifetime of 25,000 hours, the lamps reduce maintenance costs.

Product data

General information	
Lighting Technology	LED
Flux measurement reference	Sphere
Switching Cycle	20,000
Nominal lifetime	25,000 h
Cap base	E14 [E14]
Light technical	
Colour Code	922-927 [CCT of 2200K-2700K]
Luminous Flux	470 lm
Colour designation	Warm Glow (WG)
Correlated Colour Temperature	2200 2700 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	0.9

Stroboscopic effect	0.4
Operating and electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	3.4 W
Lamp current (nom.)	24 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20°C to 45°C
T-Case maximum (nom.)	70 °C


Datasheet, 2023, April 15 data subject to change

MASTER GLASS LED candles and lustres

Controls and dimming	
Dimmable	Only with specific dimmers
Mechanical and housing	
Lamp Finish	Clear
Bulb material	Glass
Bulb shape	B35 [B 35 mm]
Approval and application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	4 kWh
EPREL registration number	1109139
EU RoHS compliant	Yes


Product data		
Full EOC	871951446661600	
Order product name	MAS LEDCandleDT3.4-40WE14 927B35CLGU	
Order code	46661600	
SAP numerator – quantity per pack	1	
Numerator – packs per outer box	10	
Material number (12NC)	929003012242	
Full product name	MAS LEDCandleDT3.4-40WE14 927B35CLGU	
EAN/UPC - Case	8719514466623	

Dimensional drawing




Product	D	С
MAS LEDCandleDT3.4-40WE14 927B35CLGUK	35 mm	97 mm

Photometric data




Light Distribution Diagram - MAS LEDCandleDT3.4-40WE14 927B35CLGUK



Spectral Power Distribution Colour - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

MASTER GLASS LED candles and lustres


Photometric data




Control Streetman (C. S. Street Labour S

General uniform lighting - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

Lifetime





Life Expectancy Diagram - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

Lumen Maintenance Diagram - MAS LEDCandleDT3.4-40WE14 927B35CLGUK



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.