Automotive Fuses Mini

multicomp PRO

RoHS

Compliant



Specification


Interrupting Ratings : 1000A @ 32V DC

Body : Plastic


Metal : Zinc Alloy Strip
Rating : Blow Time

110% : 4 Hours, Minimum 135% : 0.75 to 1800 seconds 200% : 0.15 to 5 seconds 350% : 0.08 seconds, Maximum

Diagram







Part Number Table

Description	Ampere (A)	Voltage(V DC)	Color Code	Part Number
Mini Fuse	5A	32V	Tan	MP012573
	7.5A		Brown	MP012574
	10A		Red	MP012575
	15A		Blue	MP012576
	20A		Yellow	MP012577
	25A		Natural	MP012578
	30A		Green	MP012579
	2A		Lt.Gray	MP012570
	3A		Violet	MP012571
	4A		Pink	MP012572

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

