

## Product information

### Technical Details

Brand	WOL 3D
Manufacturer	CREALITY
Model number	New Ender 3 V2 Neo (1)
Colour	Black
Item Weight	10 kg
Product Dimensions	52 x 50.5 x 28 cm; 10 Kilograms
Item model number	New Ender 3 V2 Neo (1)
Item Height	28 Centimeters
Item Width	50.5 Centimeters
Compatible Device	Sd card, Personal Computer
Included Components	3D Printer

## Ender 3 V2 Neo Specification Parameter

**Molding Technology**

FDM

<b>Build Volume</b>	220x220x250mm
<b>Machine Dimension</b>	438x424x472mm
<b>Package Dimension</b>	520x505x280mm
<b>Net Weight</b>	7.8kg
<b>Gross Weight</b>	9.8kg
<b>Printing Precision</b>	±0.1mm
<b>Layer Height</b>	0.1mm-0.4mm
<b>Build Surface</b>	PC Spring Steel Magnetic Build Plate
<b>Extruder</b>	Bowden Extruder
<b>Extrusion Material</b>	Full-metal
<b>Leveling Mode</b>	CR Touch Auto-leveling
<b>Display</b>	4.3" Color Knob Screen
<b>Mainboard</b>	32-bit Mainboard
<b>Resume Printing</b>	Yes
<b>Rated Voltage</b>	100-120V, 200-240V, 50/60Hz

<b>Layer Height</b>	0.1mm-0.4mm
<b>Filament Diameter</b>	1.75mm
<b>Nozzle Quantity</b>	1
<b>Nozzle Diameter</b>	0.4mm (Standard)
<b>Nozzle Temperature</b>	up to 260 °C
<b>Heat Bed Temperature</b>	up to 100 °C
<b>Rated Power</b>	350W
<b>Slicing Software</b>	Creality Slicer/Cura/Simplify 3D
<b>Data Transmission Method</b>	Micro USB/TF Card
<b>3D File Format</b>	STL/OBJ/AMF
<b>Supported Filament</b>	PLA/PETG/ABS
<b>Supported Language</b>	Chinese/English