

Product information

97 59 14

Locator for 97 52 14

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling due to 20° angled head, low weight and short design
- Special quality chrome vanadium electric steel, oil-hardened



General

Article No.	97 59 14
EAN	4003773026976
Weight	10 g
Dimensions	20 x 10 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted