

## Product information

# 99 04 280

- To twist and cut wire in one operation: fast, reliable and economical
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

## Concreters' Nipper

(Concreter's Nippers or Fixer's Nippers)

DIN ISO 9242



### General

Article No.	99 04 280
EAN	4003773048220
Pliers	bright zinc plated
Weight	455 g
Dimensions	280 x 50 x 26 mm
Standard	DIN ISO 9242
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 2.8 mm
Cutting capacities hard wire (diameter)	Ø 1.8 mm

*technical change and errors excepted*



