

Product information

83 10 020

Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 10 020
EAN	4003773014201
Pliers	red powder-coated
Weight	2,600 g
Dimensions	560 x 82 x 30 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Clamping width	70 mm
Capacities for pipes (diameter)	Ø 2 3/4 Inch
Capacities for pipes (diameter)	Ø 70 mm
Capacities for nuts	70 mm
Inner diameter, inches	Ø 2 Inch

technical change and errors excepted

