

Product information

83 60 020

Pipe Wrench S-Type

With fast adjustment

DIN 5234



- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth

Pinch guard prevents operators' fingers being pinched

- Maximum load capability thanks to completely hardened handles
- Gripping jaws with specially hardened teeth, hardness approx. 56
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General	
Article No.	83 60 020
EAN	4003773078838
Pliers	red powder-coated
Weight	2,420 g
Dimensions	560 x 94 x 32 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Capacities for pipes (diameter)	Ø 2 3/4 Inch
Capacities for pipes (diameter)	Ø 70 mm
Capacities for nuts	70 mm
Inner diameter, inches	Ø 2 Inch
Pipe inner dia.	50 mm

technical change and errors excepted





KNIPEX Quality – Made in Germany



