

Product information

12 49 04

Torsion spring

For 12 40/50 200



- For single, multiple and fine stranded conductors with plastic or rubber insulation
- Adapts automatically to the respective cable cross-section; prevents damage to the conductor
- Cutting depth can be adjusted for different insulation materials
- With wire cutter for copper and aluminium wires, multiple stranded up to 10 mm² and single stranded up to 6 mm²
- Smoothly operating mechanism
- Stripping blades and clamping jaws easily replaceable
- Low weight
- Body: glass fibre reinforced plastic
- Blade: special tool steel, oil-hardened

General	
Article No.	12 49 04
EAN	4003773053071
Weight	4 g
Dimensions	13 x 5 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted