

Product information

71 89 950

Spare cutter head for 71 82 950

Complete with screws



- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock-absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Joint: special tool steel, forged
- Handles: steel tube, powder-coated

General

Article No.	71 89 950
EAN	4003773066842
Weight	610 g
Dimensions	71 x 33 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted