

Modern General Purpose Enclosures 1556 Series

Dual Wall-Mount or Desktop



Key Features:

- Ideally suited for mounting printed circuit boards, IoT equipment, and other small electronics.
- Can be used in a tabletop configuration using rubber feet (included) or two different wall-mount configurations using wall mount foot kit (sold separately).
- Rounded corners and face provide a more modern look.
- Lap joint construction provides protection against access of dust and splashing water.
- Available in black, gray, or white flame retardant ABS plastic with light satin texture.
- Molded from flame retardant material which carries a flammability rating of UL94-V0. For indoor use.
- Designed to meet IP54.
- Lid hardware and 4x rubber feet included with enclosure. Lid is secured with high strength #6 x 1/2" self-tapping Plastite screws.
- Aluminum inner panels are available as accessories. Sold separately. See table below.

Easy PC Board Mounting



Multiple mounting locations inside the lid and base of the enclosure allow for easy PC board mounting or can be used with Hammond aluminum panels (sold separately)



Infinitely Flexible with Desktop or Two Wall-Mounting Options

Heavy Duty Wall Flange Mount <i>(shown with accessory)</i>	Flush Wall Mount (Mounting Feet as Keyhole)	Desktop / Tabletop (Rubber Feet Included)
---	--	---





Accessories

Accessories include aluminum inner panels and 4-packs of mounting feet which can be used for flange mounting or keyhole mounting.



Black ABS	Light Gray ABS	White ABS	Length	Width	Total Height	Aluminum Inner Panel
1556BBK	1556BGY	1556BWH	80	80	45	1556BPL
1556BABK	1556BAGY	1556BAWH	80	80	60	1556BPL
1556CBK	1556CGY	1556CWH	120	80	45	1556CPL
1556CABK	1556CAGY	1556CAWH	120	80	60	1556CPL
1556DBK	1556DGY	1556DWH	120	120	45	1556DPL
1556DABK	1556DAGY	1556DAWH	120	120	70	1556DPL
1556EBK	1556EGY	1556EWH	160	120	45	1556EPL
1556EABK	1556EAGY	1556EAWH	160	120	70	1556EPL
1556FBK	1556FGY	1556FWH	160	160	45	1556FPL
1556FABK	1556FAGY	1556FAWH	160	160	70	1556FPL
1556GBK	1556GGY	1556GWH	200	160	45	1556GPL
1556GABK	1556GAGY	1556GAWH	200	160	70	1556GPL
1556HBK	1556HGY	1556HWH	200	200	45	1556HPL
1556HABK	1556HAGY	1556HAWH	200	200	70	1556HPL

Mounting Feet

Part Number (Pack of 4)	Color
1556FOOTBK-4	Black
1556FOOTGY-4	Light Gray
1556FOOTWH-4	White

Replacement Hardware

Part Number (Pack of 24)	Type
SC527-50	Cover Screw
SC526-50	PC Board Screw
SC556-50	Mounting Foot Screw

Replacement Rubber Feet (24-pack)

Part No.	1421T6CL
----------	----------

Tags: **ABS, wallmount, feet, PCB, mounting, IOT, flush mount, tabletop, desktop, inner panel**

Data subject to change without notice

© 2023. Hammond Manufacturing Ltd. All rights reserved.