TE Internal #: 169404

TE Internal Description: CERTI-LOK DIE

View on TE.com >





Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





TE Part # CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part # CAT-P592-SP118
PIDG Spade Tongue Terminals



TE Part # CAT-P592-SH816
PIDG Short Spring Spade Tongue
Terminals



TE Part # CAT-P592-ST433
PIDG Stepdown Butt Splices



TE Part # CAT-P592-F614
PIDG Flanged Spade Tongue
Terminals



TE Part # CAT-P592-K742 PIDG Knife Disconnect Splices



TE Part # CAT-P592-L853
PIDG Long Spring Spade Tongue
Terminals



TE Part # CAT-P592-P624
PIDG Piggy Back FASTON Terminal



TE Part # CAT-P592-F266
PIDG FASTON Receptacle Quick
Disconnects



TE Part # CAT-P592-T116
PIDG Pre-Insulated Diamond Grip Tabs



TE Part # CAT-P592-F766
PIDG Formed Wire Pins



TE Part # CAT-P592-SL56
PIDG Slotted Ring Tongue Terminals



TE Part # CAT-P592-H763
PIDG Hook Tongue Terminals



TE Part # CAT-P592-SH93
PIDG Shur Plugs



TE Part # CAT-P592-R2456
PIDG Rectangular Tongue Terminals



TE Part # 323039 PIDG R OFS 22-16COM22-18MIL 6



TE Part # CAT-P592-B98
PIDG Butt Splices



TE Part # CAT-P592-R472
PIDG Radiation Resistant C Rings
/Spades



TE Part # 160138
PIDG RING TONGUE



PIDG R 22-16 COMM 22-18 MIL 4

Customers Also Bought





TE Part #1-2823445-1 M12 D-M-4, CRIMP, CAT5 RADOX 6.6 MM, H&S



TE Part #K1166104
Battery Disconnector 35-414-131-S-900



TE Part #1757824-2 AMPLIMITE,ASY,RCPT,STD,90,ZN,2





TE Part #8-1768018-6 EET-2576P-9



TE Part #169403 LOCATOR



TE Part #169400 CERTI-LOK FRAME W/O DIES





Documents

Datasheets & Catalog Pages

Bottoming Dies

English

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Instruction Sheets

Instruction Sheet (U.S.)

English