

2 Pc Cobra Water Pump Pliers Set

00 31 20 V01 US



- The KNIPEX Cobra® Water Pump Pliers are the perfect gripping pliers for every application. The Cobra Pliers will grip any shaped object - round, square, hex or flat with a bite like no other pliers. This very popular two-piece set will grip up to 2"
- Adjustment at the touch of a button directly on the workpiece
- Fine adjustment for optimum adaptation to different size workpieces and a comfortable gripping position
- Self-locking on pipes and nuts: no slipping off the workpiece and low handforce required

- Gripping surfaces with special hardened teeth, teeth hardness (approx. 61 HRC): low wear and reliable gripping
- Box-joint design: high stability because of double guide
- Pinch guard prevents operators' fingers being pinched
- Reliable catching of the hinge bolt: no unintentional shifting
- Set includes two (2) Cobra® Water Pump Pliers: 87 01 180 (7 1/4") and 87 01 250 (10")

Technical details

Part Number: 00 31 20 V01 US

UPC: 843221020576

Country of Origin: Germany

Width: 4"

Height: 1 1/2"

Weight: 1.24 lbs.

1000 Volt Insulated: No

ESD Indicator: No

Spring Loaded: No

Material Type: Chrome vanadium electric steel, forged, oil-hardened

Handle Type: Non-slip plastic

Gripping Surface: Serrated

Surface Finish: Polished jaws

Joint Type: Box-joint

Number of Adjustment Positions: 18 (87 01 180); 25 (87 01 250)

Jaw Length: 1 1/16" (87 01 180); 1 3/8" (87 01 250)

Max Jaw Opening - Round Pipe: 1 1/2" (87 01 180); 2" (87 01 250)

Max Jaw Opening - Hex: 1 27/64" (87 01 180); 1 3/4" (87 01 250)

Max Jaw Opening - Working Capacity: 1 1/2" (87 01 180); 2" (87 01 250)

Color: Red

DIN: DIN ISO 8976

Reach: does not contain SVHC

RoHS: not applicable