40 Piece Terminator Blue Impact Bit Set

SKU: 70297



DESCRIPTION:

40 PC Terminator Bit SetTerminate screws faster—and with fewer broken bits. Wiha's TerminatorBlue Impact Bits—proven toughest. TerminatorBlue Bits are impact rated for power tools and rigorously heat-treated to produce a bit lasting 120 times the service life compared to standard bits. Wiha's specially designed torsion zone absorbs 30 times the impact energy compared to standard bits, allowing a maximum torsion flex that goes

unmatched. With TerminatorBlue Impact Bits you get the tightest-fit precision-machined driver tips from the company that sets the standard for precision. Wiha's exact-fit tips eliminate excessive bit-wobble for increased driver accuracy. The result is a highly stable engagement with the screw head and a reduction in fastener cam-out that can lead to injury or damage to finished materials.

- Set Includes: Phillips #1, #2, #3x25mm, #1, #2, #3x50mm, #2x89mm | Square #1, #2, #3x25mm, #1, #2x50mm, #3x89mm | Torx T15, T20, T25, T30x25mm, T20, T25, T30, T40x50mm, T20, T25, T30x89mm | Nut Setter 5/16x76mm, Nut Setter 3/8x76mm | Bit Holder 1/4x60mm
- Energy-absorbing Torsion Zone for 30 times performance over Wiha standard bits
- Computer-controlled heat treatment for 120 times service-life over Wiha standard bits
- TST Torsion Stabilizing Technology for reduced tip stress and a maximum flex torsion zone
- Exact fit precision machined tips for reduced cam-out
- CVM premium quality tool steel for strength and durability
- Universal 1/4" Hex Shank
- Impact rated for power tool applications
- Minimum hardness tolerance of 61 RHC +/- 1
- Stack-N-Lock
- The closed box itself is 5.0 x 8.0 x 2.25

SPECS:

■ SKU: 70297

UPC: 084705702971

Country of Origin: Vietnam

Packaging: Clamshell

Weight lb: 1.8 lb

Case Pack Quantity: 4