

Data sheet

Commercial Art.No.: 83.040.0106.0

IP switch WIENET UMS 8G

wieNET IP Switch, 8 TP-RJ45-Ports, transfer rate 10/100/1000 MBit/s, unmanaged switch, Autonegotiation, Autosensing, Autocrossing-function, redundant power supply, supply voltage: 9-48 V, vertical mount



Commercial Art.No.	83.040.0106.0
EAN	4049088132742
Order Unit	1

certificates / approvals



Technical data

Allgemein

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP50
housing material	metal
manageable	no
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	yes
number of ports 10/100 Mbps RJ45	0
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 10/100/1000 Mbps RJ45	8
number of ports 100 Mbps SC	0
number of 100 Mbps ST-Ports	0

technical data

voltage type	DC
min. operating temperature	-10 °C
max. operation temperature	70 °C
redundant power supply	2 power inputs

supply circuit

voltage type	DC
--------------	----

operating voltage min.	9 V
operating voltage max.	48 V

dimensions

depth	95 mm
width	30 mm
height	120 mm

classification


ECLASS 11	
ECLASS 8.1	19170106
ETIM 9.0	EC000734
ETIM 8.0	EC000734
ETIM 7.0	EC000734
ETIM 6.0	EC000734
ETIM 5.0	EC000734
ETIM 4.0	EC000734

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant

Accessories

Commercial Art.No.:	Article-type description:	Description:
78.999.4000.0	patch-cables MOD ZBH RJ45 0,25 m	
78.999.4100.0	patch-cables MOD ZBH RJ45 0,5 m	
78.999.4200.0	patch-cables MOD ZBH RJ45 1,0 m	
78.999.4300.0	patch-cables MOD ZBH RJ45 2,0 m	
78.999.4400.0	patch-cables MOD ZBH RJ45 3,0 m	
78.999.4500.0	patch-cables MOD ZBH RJ45 5,0 m	
78.999.4600.0	patch-cables MOD ZBH RJ45 7,5 m	
78.999.4700.0	patch-cables MOD ZBH RJ45 10 m	



Weitere Angaben siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.

Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD-Zeichnung, keine manuellen Änderungen
CAD-Drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt:
Sheet:



Werkstoff/ Material

2015

Tag/ Date

Name

Zeichnung Nr./ Drawing No.

Maßstab/Scale

gezeichnet
drawn

16.03.

Koetzner

83.040.0106.0 01K

geprüft
checked

Normgepr.
Stand. check

Maße in mm/Dimensions are in mm

Datei/ File: 035951__A01K.DCD

Ersatz für/ Replacement for:

① 07.12.17

Index Datum/ Blatt
Date/ Sheet

Änderung/ Revision



wieland

www.wieland-electric.com

Type

Benennung/ Title

Teilespezifikation /
Component specification

IP-SWITCH / IP SWITCH
wienet UMS 8G