

Eaton CE15JN3AB

Catalog Number: CE15JN3AB

Eaton XT IEC contactor, 60A, 110-120 Vac, 50-60 Hz, 60A, Frame J, 50-60 Hz, 5 hp, Steel mounting plate, Three-pole, Non-reversing, No overload relay, Freedom, Contactor

General specifications

Product Name

Eaton XT IEC contactor

Catalog Number

CE15JN3AB

UPC

782113973449

Product Length/Depth

4.22 in

Product Height

4.27 in

Product Width

2.56 in

Product Weight

2.12 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

DIN VDE 0600
ISO 9000

Certifications

CSA Certified
IEC Rated
UL Listed

Catalog Notes

No enclosure



Product specifications

Frame size

J

Coil voltage

110-120 Vac, 50-60 Hz

Series

Freedom

Type

Contactors

Relay

No overload relay

HP rating - max

5 hp

Continuous ampere rating

60 A

Frequency rating

50-60 Hz

Operation

Non-reversing

Mounting method

Steel mounting plate

Amperage Rating

60A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - CE15JN3AB](#)