

# Product Specification PDF

Date	<b>Correct as of 31st Aug 2023</b>
Brand	<b>C.K</b>
Product	<b>T9740</b>
Description	<b>Site Light 5000lm 18V</b>
Barcode	<b>5013969249576</b>
Commodity code	<b>8513100000</b>
Country of origin	<b>CN</b>



## Features & Benefits

- ~ High powered site light with adjustable LED. ~ Heavy duty IK08 rated design for increased impact resistance. ~ Tactile on/off switch with +/
- brightness function. ~ CKlearView LED for accurate colour rendering. ~ 4 x selectable power output (5000, 3750, 2500 and 1250lm). ~ Integrated pivot stand to adjust working angle. ~ IP65 rated against dust and water ingress. ~ Threaded base for tripod mounting. ~ Battery level indicator. ~ Compatible with standard 18V power tool batteries using the included adaptors (eg. Bosch, Dewalt, Makita, Metabo and Milwaukee).

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	3	48
Width mm	262	275	570	1200
Depth mm	171	172	363	800
Height mm	202	225	245	900
Weight	1570	1820	7850	114
Packaging Information	Card use	-	-	Pallet
	Card gms	-	-	-
	Plastic use	PE bag	-	-
	Plastic gms	10	-	-
	Metal use	-	-	-
	Metal gms	-	-	-
	Timber use	-	-	-
	Timber gms	-	-	-