


PXM6010/04S/CR/0507 Datasheet

Product Name // Flex Cable Connector PXM6010 Series 4
Contact Socket Crimp/Solder Termination (contacts available separately) 5mm-7mm Cable (White Gland) Metal Body No Braid Termination

 [View Product Page](#)



// **Product Description:**

- Flex Cable Connectors
 - Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
 - 30 degree push twist locking, tamperproof lock prevents accidental un-mating
 - Socket
 - 4 Contacts
 - Crimp/solder termination with contacts and fitting tool available separately
- Metal Body No Braid Termination
 - Cable acceptance 5mm-7mm diameter
 - Gland Pack PXP6088 available separately to accomodate all sizes
 - PXM6081 Sealing Cap available separately to maintain IP rating of unmated connectors
 - Mate with PXM6011 Series Inline and PXM6012 Series Front Panel Mount Connectors

// **General Information:**

Product Display Title:	Flex Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Body Colour:	Metallic Grey
Body Material:	Brass
Body Material Type:	Metal Body No Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	10A, 4A, 7A
Diameter Over Coupling Ring Mm:	32mm
Function:	Flex Cable Connector
Insulation Resistance:	>10 ⁶ MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	7mm
Min Cable Entry Size:	5mm
Max Contact Accomodation Awg:	20AWG
Min Contact Accomodation Awg:	16AWG
Max Contact Accomodation Mm2:	1.5mm2
Min Contact Accomodation Mm2:	0.5mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	4 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-11 Test Ka Salt Mist
Voltage Max:	277V

// **Product PDF Links**

-  6000 Series power connectors...
-  6000 Series metal body power...

// **Product 3D CAD Model Links**

-  PXM6010/04S/CR/05073D CAD Model



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)