




8160

**Micro-Bevel® Precision Cut
Diagonal Cutter with Oval Head &
ESD Safe Handle 0.4-2 mm**











PRODUCT DETAILS

- 80 Series precision diagonal and stripping cutter
- ESD safe mono-material handles with return spring
- Micro-bevel cut
- The cutting capacity given is for copper wire
- Suitable for cutting Cu
- High performance alloyed steel
- Burnished finish
- Numerically controlled machine grinding guarantees edge angle accuracy & contact, increases the tools reliability & consistency
- Precision induction hardened edges 63-65 HRC
- Screw joint that minimizes friction & maximizes alignment of cutting edges
- Ideal for wire harness work & standard printed circuit board assembly
- Also valid for stripping



PRODUCT ATTRIBUTES

Product: **8160**

	Oval		L		Micro-Bevel®
	0.4-2.0 mm		0.02-0.08 in		0.3-0.8 mm
	0.01-0.03 in	A	125 mm	A	4.92 in
B	16 mm	B	0.63 in	C	16 mm
C	0.63 in	D	8 mm	D	0.31 inch
F	1.6 mm	F	0.06 in		97 g
Ω	Dissipative				