

USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 15 ft. (4.57 m), Black

MODEL NUMBER: U009-015-RJ45-X











Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

Features

Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

Top-Quality Construction for Top-of-the-Line PerformanceNo extra software or external power is required to use this 15-ft. (4.57 m) cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-015-RJ45-X is compatible with Windows (up to 11), Mac (up to 10.12) and Linux (up to Redhat 9.0) operating systems.

Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 15-ft. (4.57 m) cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

Applications

 Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port
- Windows (up to 11), Mac (up to 10.12), or Linux (up to Redhat 9.0) operating systems

Package Includes

 U009-015-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 15-ft. (4.57 m)

Specifications

OVERVIEW		
UPC Code	037332222121	
Technology	Cat5/5e; USB	
Host Connector	USB A (MALE)	
POWER		
USB Power Delivery (PD) Charging Support	No	



PHYSICAL		
Color	Black	
Material of Construction	PVC, PE	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Outer Diameter (OD)	5.5mm; 4.7mm +/- 0.15	
Wire Gauge (AWG)	26	
Cable Length (ft.)	15	
Cable Length (m)	4.57	
Cable Length (in.)	180	
Cable Length (cm)	457	
Unit Packaging Type	Polybag	
Unit Weight (lbs.)	0.3968	
Unit Weight (kg)	0.18	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Relative Humidity	0% to 90% RH (Non-Condensing)	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	RJ45 (MALE)	
FEATURES & SPECIFICATIONS		
USB Specification	USB 1.1 (up to 12 Mbps)	
IP68 Rated	No	
IP20 Rated	No	
Suspend Mode Support	Yes	
Driver Required	Yes	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.