2-1437012-8 < ACTIVE

AMPLIMITE

TE Internal #: 2-1437012-8 IDC D-Sub Connectors View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023

Halogen Content

(235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach

IDC D-Sub Connectors



Compatible Parts



Customers Also Bought



 TE Part #1393248-5
 TE Part #3-2176349-3
 TE Part #5212046-1

 W33-S1N1Q-10=W33
 CRGCQ 2512 4K7 1%
 7 CIRC DIN RCPT GRND SHLD

Documents

Product Drawings 609-007-1=HDW IDC JACKSOCKET A

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1437012-8_H.2d_dxf.zip

English

3D PDF

3D

Customer View Model ENG_CVM_CVM_2-1437012-8_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1437012-8_H.3d_stp.zip

2-1437012-8

IDC D-Sub Connectors



English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Environmental Compliance

MD_2-1437012-8_12232013922_dmtec

English

MD_2-1437012-8_12232013922_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English