



Main

Range	Spacial
Extended range	Spacial SF
Application	Multi-purpose
Product or Component Type	Suitable enclosure
Enclosure nominal height	78.74 in (2000 mm)
Enclosure nominal width	31.50 in (800 mm)
Enclosure nominal depth	23.62 in (600 mm)
Enclosure mounting	Floor-standing
Device composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle door 1 rear panel 1 roof 1 mounting plate

Complementary

Structure type	Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure Vertical uprights joined with top and bottom frames
Door type	Solid front
Number of doors	Front 1
Door opening side	Reversible 120 °)
Lock type	4 points lock, handle with 5 mm double bar insert front door
Mounting plate description	Plain
Type of gland plate	Without gland plate
Accessibility for operation	Front Rear Sides of enclosure
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame galvanised steel Uprights galvanised steel Door sheet steel Panels sheet steel Hinge zamak Handle polyamide 6 with 30 % fibre glass
Surface finish	Epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)
Product Weight	324.12 lb(US) (147.019 kg)

Environment

Standards	IEC 62208
NEMA Degree of Protection	NEMA 3R/12
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80035-ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	3606485117690
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.17 in (69.0 cm)
Package 1 Width	33.27 in (84.5 cm)
Package 1 Length	83.86 in (213.0 cm)
Package 1 Weight	291.01 lb(US) (132.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------