



Main

| | |
|---------------------|--|
| Range | Thalassa |
| Product name | Thalassa TBP |
| Device Application | Multi-purpose |
| Category | Industrial box |
| Height | 4.57 in (116 mm) |
| Width | 2.91 in (74 mm) |
| Depth | 2.44 in (62 mm) |
| Internal height | 4.13 in (105 mm) |
| Internal width | 2.56 in (65 mm) |
| Internal depth | 2.17 in (55 mm) |
| Enclosure mounting | Wall mounted |
| Device composition | 1 body 1 cover 4 cover screw |
| Quantity per Set | Set of 5 |
| Body type | One piece moulded |
| Type of front cover | Low plain cover |
| Cover fixing | Metal screws |
| Lock type | Captive screw flat outside sealed area |
| Removable parts | Cover by captive screws |

Complementary

| | |
|-----------------------------|---|
| Material | polycarbonate |
| Color | Gray RAL 7035) |
| Standards | UL 508 A IEC 62208 |
| Product Certifications | TÜV UL |
| Electrical Insulation Class | Class II |
| Mounting location | Outdoor (with canopy or shelter and anticondensation valve) |
| Product Weight | 0.27 lb(US) (0.124 kg) |

Environment

| | |
|-------------------------------------|------------------------------|
| IP degree of protection | IP66 conforming to NEMA 4.4X |
| IK degree of protection | IK08 IEC 62262 |
| Fire resistance | 1760 °F (960 °C) |
| Ambient Air Temperature for Storage | 5...140 °F (-15...60 °C) |
| Operating temperature | -13...176 °F (-25...80 °C) |







Ordering and shipping details

| | |
|-------------------|-----------------------------------|
| Category | 80033-ENCLOSURE SYSTEMS POLYESTER |
| Discount Schedule | ES1 |
| GTIN | 3606480165603 |
| Returnability | No |
| Country of origin | HU |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.67 in (1.7 cm) |
| Package 1 Width | 1.02 in (2.58 cm) |
| Package 1 Length | 2.63 in (6.68 cm) |
| Package 1 Weight | 4.37 oz (124 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 13.15 in (33.4 cm) |
| Package 2 Width | 4.88 in (12.4 cm) |
| Package 2 Length | 3.35 in (8.5 cm) |
| Package 2 Weight | 21.87 oz (620 g) |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 105 |
| Package 3 Height | 23.62 in (60 cm) |
| Package 3 Width | 15.75 in (40 cm) |
| Package 3 Length | 15.75 in (40 cm) |
| Package 3 Weight | 31.44 lb(US) (14.26 kg) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|