



Main

Range	Spacial
Product name	Spacial S3DB
Application	Terminal application
Category	Compact enclosure
Enclosure nominal height	19.69 in (500 mm)
Enclosure nominal width	15.75 in (400 mm)
Enclosure nominal depth	5.91 in (150 mm)
Door type	Solid
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Installation accessory type	Wall-mounting Horizontal or vertical position
Product destination	For equipping with terminal
Device composition	1 body 1 door 1 lock

Complementary

Body type	Gutter-shaped front rail double sheet thickness Single piece body
Number of doors	Front face 1
Door opening side	Reversible 180 °)
Lock type	3 mm double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges
Material	steel
Surface finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	BV DNV GL UL LR cUL
Product Weight	15.84 lb(US) (7.186 kg)

Environment

NEMA Degree of Protection	NEMA 4X/13
IK degree of protection	IK10 IEC 62262
IP degree of protection	IP66 IEC 60529

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480158735
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.87 in (20.0 cm)
Package 1 Width	16.34 in (41.5 cm)
Package 1 Length	20.08 in (51.0 cm)
Package 1 Weight	15.84 lb(US) (7.186 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	36
Package 2 Height	82.28 in (209.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	599.66 lb(US) (272.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------