



Main

Range	Spacial
Extended range	Spacial SF
Application	Multi-purpose
Product or Component Type	Suitable enclosure
Enclosure nominal height	86.61 in (2200 mm)
Enclosure nominal width	47.24 in (1200 mm)
Enclosure nominal depth	23.62 in (600 mm)
Enclosure mounting	Floor-standing
Device composition	2 sliding rails 4 mounting plate bracket 1 structure 1 rear panel 1 roof 1 mounting plate 2 door 1 locking system with handle 1 blocking system left door

Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Door type	Solid front
Number of doors	Front face 2
Door opening side	Left 120 °) Right 120 °)
Lock type	4 points lock, handle with 5 mm double bar insert front right door
Mounting plate description	Plain
Type of gland plate	Without gland plate
Accessibility for operation	Sides of enclosure Rear Front
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame galvanised steel Uprights galvanised steel Door sheet steel Panels sheet steel Hinge zamak Handle polyamide 6 with 30 % fibre glass
Surface finish	Epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)
Product Weight	517.71 lb(US) (234.827 kg)

Environment

Standards	IEC 62208
NEMA Degree of Protection	NEMA 3R/12
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80035-ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	3606485117911
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	91.73 in (233.0 cm)
Package 1 Width	49.02 in (124.5 cm)
Package 1 Length	27.17 in (69.0 cm)
Package 1 Weight	517.71 lb(US) (234.827 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------