



Main

Range	Spacial
Product name	Spacial S3HF
Application	Industrial Application
Category	Compact enclosure
Enclosure nominal height	19.69 in (500 mm)
Enclosure nominal width	15.75 in (400 mm)
Enclosure nominal depth	7.87 in (200 mm)
Door type	Solid
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Installation accessory type	Wall-mounting
Device composition	1 body 1 door with lock 1 mounting plate

Complementary

Body type	Single piece body
Number of doors	Front face 1
Lock type	3 mm double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body aluzinc
Surface finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 60529
Net Weight	26.46 lb(US) (12 kg)

Environment

Electromagnetic compatibility	EMC immunity
IK degree of protection	IK10 IEC 62262
IP degree of protection	IP55

Ordering and shipping details

Category	80035-ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	3606480212826
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.46 in (21.5 cm)
Package 1 Width	16.14 in (41 cm)
Package 1 Length	20.28 in (51.5 cm)
Package 1 Weight	26.46 lb(US) (12 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------