

Product data sheet

Characteristics

NSYEC1261

Spacial SF 1 entry cable gland plate - fixed by clips - 1200x600 mm



Main

Range	Spacial
Product or Component Type	Cable gland plate
Accessory / separate part category	Cable management accessory
Anwendung	Multi-purpose
Range compatibility	Spacial (Spacial SF)
Mounting Location	Enclosure bottom
Cable gland type	Standard
Cable entry	1 entry
Device composition	Fixing elements 1 plate Self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity per Set	Set of 1
Material	Galvanised steel

Complementary

Height	1.38 in (35 mm)
Width	Nominal 47.24 in (1200 mm) Useful 40.00 in (1016 mm)
Depth	Nominal 23.62 in (600 mm) Real 20.47 in (520 mm)
Thickness	0.06 in (1.5 mm)

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606485126388
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	13.78 in (35.0 cm)
Package 1 Length	20.47 in (52.0 cm)
Package 1 Weight	15.22 lb(US) (6.902 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	40
Package 2 Height	18.90 in (48.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	637.31 lb(US) (289.08 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or intended user to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <input checked="" type="checkbox"/> EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	<input checked="" type="checkbox"/> China RoHS Declaration
RoHS exemption information	<input checked="" type="checkbox"/> Yes
Environmental Disclosure	<input checked="" type="checkbox"/> Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------